

MicroSeal® 1200

Sealed Edge Cleanroom Laundered 100% Polyester Knit Wiper

MicroSeal® 1200 is an ultrasonically sealed edge cleanroom laundered wiper required for ISO Class 3 and above environments composed of 100% continuous filament polyester knit fabric. This combination of properties provides MicroSeal® 1200 with the high level of cleanliness, abrasion resistance and chemical compatibility required for ISO Class 3 and above environments and applications requiring critical control of contaminants combined with superior performance.



Key Attributes

- 100% continuous filament polyester knit
- Ultrasonically sealed edge for reduced fibre contamination
- Laundered and packaged in Berkshire's ISO Class 4 cleanroom

Benefits

- Critically low particles, fibres, ions and extractables
- High abrasion resistance
- Chemically compatible with IPA, Acetone and other solvents
- High absorbency
- Weight and caliper provide an excellent hand for cleaning rough surfaces

Applications

- Designed for use in ISO Class 3 and higher cleanroom environments
- Designed for the highest level of contamination control in critical processing applications
- Oxidation, Metallization, CVD or Photolithography processes
- Chamber cleaning and CMP processing
- Stencil and other print roll cleaning applications
- Steam autoclavable for aseptic applications
- Cleaning of medical device products
- Applying and removing cleaning and disinfecting solutions

Other Class 3 and above wipers

- MicroSeal SuperSorb®
- UltraSeal® 3000
- MicroSeal® VP
- ValuSeal® LP
- ValuSeal® HA
- ValuSeal® 1500

Value Pack Option

The value pack option provides the same great performance in a more economical bulk packaging format.

Pre-Wetted Option

The same wiper material can be provided in pre-wetted formats for reduced VOC emissions, increased convenience, increased productivity, improved solvent control and cleaning protocol repeatability and reduced costs.

Sterile Validated Option

For aseptic processing areas, the same wiper material can be provided in a gamma irradiated validated sterile to a 10⁻⁶

www.berkshire.uk.com

Contact: Tel + 44 1953 562800
enquiries@berkshire.uk.com

America	Tel 1 413 528 2602	info@berkshire.com
Europe	Tel + 44 1953 562800	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	enquiries@berkshire.com.sg
Japan	Tel 81 3 4530 9883	master@berkshire.co.jp

Technical Data:

Attribute		Units	Value	Test Method
Basis Weight		g/m ²	154	TAPPI T-410
Caliper		µm	507	TAPPI T-411
Fibres	≥100µm	fibres/cm ²	0.036	IENT-RP-CC004.4 Sec 7.1.3/Sec 7.2.2 modified
Particles	≥0.5µm	x10 ³ /cm ²	0.40	IENT-RP-CC004.4 Sec 7.1.3/Sec 7.2.1 modified
Sorbency	Capacity	mL/m ²	512	IENT-RP-CC004.4 Sec 9.1 / Sec 9.2 modified
	Efficiency	mL/g	3.3	
	Rate	seconds	1	
Non-Volatile Residue	DI Water	g/m ²	0.0045	IENT-RP-CC004.4 Sec 8.1.2
	IPA	g/m ²	0.0082	
Ions	Na ⁺	ppm	0.17	IENT-RP-CC004.4 Sec 8.2.2
	K ⁺	ppm	0.017	
	Ca ⁺⁺	ppm	0.082	
	Mg ⁺⁺	ppm	0.0090	
	Cl ⁻	ppm	0.20	

Notes:

- Technical data represented in this table are typical values at the time of publication. These should not be used as product specifications.
- Due to differences in test methods applied and equipment utilised by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
- Third party testing can be performed upon request

Order Information:

Product	Number	Size	Shts/pk	Pks/cs	Style
MicroSeal® 1200	MS1200.0404B.10	4x4" (10x10cm)	600	10	Value Pack
MicroSeal® 1200	MS1200.0909.8	9x9" (23x23cm)	100	8	Stacked
MicroSeal® 1200	MS1200.1212.6	12x12" (30x30cm)	100	6	Stacked

Other Berkshire products



Wipers




Mop Systems



Face Masks



Glove Liners



Documentation Systems



Swabs

www.berkshire.uk.com

Contact: Tel + 44 1953 562800 / info@berkshire.uk.com